



WE  
CONSIDER  
FOR  
OUR DOCTORS  
& BEAUTICIANS

### THE WORLD'S FIRST STRAIGHT-THROUGH DIODE LASER HANDLE



Operated by one person  
with one hand only



Effectively reducing  
fatigue by 60%,  
not tiring and cool



The handle comes with  
a control screen, easy control  
the overall situation

### TECHNICAL SPECIFICATIONS:

Laser Wavelength	808nm/755nm/940nm/1064nm
The Light Guide Crystal	Sapphire
Handpiece	450g
Spot Size	15*1 5mm;15*30mm;8Φ
Repetition Frequency	1-10Hz
Energy Density	1~55J/cm²
Laser Cooling Temperature	-5℃ - 5℃
Power Supply	AC230V,50Hz / AC110V, 60Hz
Cooling System	Air + Water + Semiconductor + Sapphire
Rated Power	3000w

# EpiluxDiode

PRO

## Newest Revolutionary Hair Removal Diode Laser Debuts globally

WELCOME TO A NEW WORLD!





# EpiluxDiode

PRO


## NEWEST REVOLUTIONARY HAIR REMOVAL DIODE LASER DEBUTS GLOBALLY

- Germany LIMO Collimator Lenses
- 360° Cooling Peltier
- Germany LIMO Focusing Lens



### Additional Hair Analyzer Handle


The world's first AI diode laser technology, equipped with hair detection to intelligently recommend the best parameters.



### 3 Changeable Spot Sizes Handle

#### ① One handle three spot

15\*15mm, 15\*30mm, 8\*8mm can be switched freely



#### ② Four in1 Personalized Platform

808nm, 755nm, 940nm, 1064nm wavelengths, from single wave to 4 bands, what you want is what I will do.



### World 's First Optical Waveguid Nose Tip

First Nose tips with optical waveguide jointly developed by German LIMO

+100% Treatment Gentleness

+100% Treatment Effect





# EpiluxDiode

—PRO—

WE  
CONSIDER  
FOR  
OUR DOCTORS  
& BEAUTICIANS



## THE WORLD'S FIRST STRAIGHT-THROUGH DIODE LASER HANDLE



Operated by one person  
with one hand only



Effectively reducing  
fatigue by 60%,  
not tiring and cool





The handle comes with  
a control screen, easy control  
the overall situation




## ONE HANDLE THREE SPOT

(15\*15mm, 15\*30mm, 8\*8mm) can be switched freely




01



### Germany LIMO Collimator Lenses

The spot uniformity is increased by **100%**  
The energy density is increased by **20%**  
The efficacy is increased by **50%**


02



### 360° Cooling Peltier

Cooling reaches **-18°** in 2 minutes  
Skin contact cooling is increased by **300%**

03





### Germany LIMO Focusing Lens


Using German **LIMO** gemstone light guide crystal, Spot size adjustable by magnetic suction, just to please you

## FIRST NOSE TIPS WITH OPTICAL WAVEGUIDE JOINTLY DEVELOPED BY GERMAN LIMO


Treatment gentleness increased by **100%**  
While the effect increased by **100%**



- Easily treat areas that are normally hard to reach, including the ears, nostrils and glabella.



- For forehead, upper lips, cheeks, More accurate and effective.



- Fast treatment for large areas, Save treatment time and sessions.







# EpiluxDiode

PRO



## WIRELESS UPGRADE OF ANDROID SYSTEM

Massive data storage. To create constant surprises for you, I never stop working hard to upgrade.



## 15.6-inch Ultra-clear Android screen

I know you like as biggest as it could









# ACTUAL EFFECT OF DEPILATION

## UNDERARMS



before



after

## BACK



before



after

## ABDOMEN



before



after

## LIP



before



after

## CHIN



before



after

## BIKINI AREA



before



after

## LEGS



before



after

## CHEST



before



after

## CHEEK



before



after